

The crystallizers of the CRN series have been designed to treat PET in amorphous granules and flakes of bottles, etc. There are 9 models with capacities ranging from 300 to 8000 dm³.



TECHNICAL SPECIFICATIONS:



- Control with a PLC Siemes and touchscreen operator interface.
- Stainless-steel hopper equipped with a vertical agitation system. Powered by epicyclic gearmotors with a low number of revolutions.
- High-efficiency soundproof fan.
- Electric-type heating chamber or gas exchanger.
- Cyclone installed on the return pipe of the process air.

ACCESSORIES

- Rotary valve for loading and unloading.
- Pneumatic feeding and extraction system.
- Oil condensation system.

ADDED VALUE:

- Uniform crystallization of the polymer without any degradation.
- Purification of the oil contained in the re-grind material.
- Indispensable before extrusion processes on single-screw and bi-screw extruders. It makes the process stable and safeguards the loss of IV.
- A perfect choice to restore the values of crystallinity of the materials after granulation processes.



TECHNICAL DATA		CRN50	CRN300	CRN600	CRN1000	CRN1500	CRN2000	CRN3000	CRN4000	CRN7000
Type/Shape PET	GR SC	GR SC	GR SC	GR SC	GR SC	GR SC	GR SC	GR SC	GR SC	GR SC
Throughput	Kg/h	25 15	125 80	250 160	400 270	600 400	800 550	1200 800	1600 1000	2800 1800
Airflow	m3/h	60	300	600	1000	1500	1500	2500	3200	5600
Reel rotation	rpm	2.5	2.5	2.5	2.5	1.5	1.5	1.5	1.5	1.5
Static pressure Δp	mbar (20°C)	60	60	60	100	100	100	140	140	140
Diameter of pipes	mm	50	89	189	200	200	200	250	250	300
Heating power	kW	3.5	18	18	27	58	54	81	94.5	135
Gearmotor power	KW	0.25	1.5	1.5	1.5	2.2	2.2	4	4	7.5
Total power	KW	4.1	23	23	35.1	72.3	72.3	104.6	118.1	173.6
Dimensions	H	1188	3531	4229	4900	5200		5800	6321	7554
	D	766	968	968	1860	2144		2800	2800	3380
	W	672	968	968	1317	1570		2120	2120	2860

GR = Granules SC = Flakes